

RT-N66R

Network Standard IEEE 802.11a, IEEE 802.11b, IEEE 802.11g, IEEE 802.11n, IPv4, IPv6

Product Segment N900 ultimate performance : 450+450 Mbps

Coverage Large homes

Data Rate 802.11a : 6,9,12,18,24,36,48,54 Mbps
802.11b : 1, 2, 5.5, 11 Mbps
802.11g : 6,9,12,18,24,36,48,54 Mbps
802.11n : up to 450 Mbps

Antenna Detachable dBi antenna x 3

Transmit/Receive MIMO technology
2.4 GHz 3 x 3
5 GHz 3 x 3

Memory 32 MB Flash
256 MB RAM

Operating Frequency 2.4 GHz / 5 GHz

Encryption 64-bit WEP, 128-bit WEP, WPA2-PSK, WPA-Enterprise , WPA2-Enterprise , WPS support

Firewall & Access Control Firewall: SPI intrusion detection, DoS protection
Access control: Parental control, Network Service filter, URL filter, Port filter

[Chat With Us](#)

Management UPnP, DLNA, DNS Proxy, DHCP, NTP Client, DDNS, Port Trigger, Port Forwarding, DMZ

WAN Connection Type Internet connection type : Automatic IP, Static IP, PPPoE(MPPE supported), PPTP, L2TP
Multicast Proxy support

Ports RJ45 for 10/100/1000/Gigabits BaseT for LAN x 4
USB 2.0 x 2

Features **Airtime Fairness**

SmartQoS

- WMM
- User definable rules for IP/MAC/Port
- Upload and download bandwidth management
- ACK/SYN/FIN/RST/ICMP with highest priority

Parental Control

Guest Network : 2.4 GHz x 3, 5 GHz x 3

VPN server : IPsec Pass-Through, PPTP Pass-Through, L2TP Pass-Through, PPTP Server, OpenVPN Server

VPN client : PPTP client, L2TP client

Enhanced media server (AiPlayer app compatible)

- Image : Jpeg
- Audio : mp3, wma, wav, pcm, mp4, lpcm, ogg
- Video : asf, avi, divx, mpeg, mpg, ts, vob, wmv, mkv, mov

AiCloud personal cloud service

3G/4G data sharing

Printer Server

- Multifunctional printer support (Windows only)
- LPR protocol support

Download Master

- Support bt, nzb, http, ed2k
- Support encryption, DHT, PEX and magnet link
- Upload and download bandwidth control
- Download scheduling

AiDisk file server

- Samba and FTP server with account management

Dual WAN

IPTV support

Button WPS Button, Reset Button, Power Button

LED Indicator LAN x 4

WAN x 1

Wi-Fi x 2

USB x 1

Chat With Us

Power Supply AC Input : 110V~240V(50~60Hz)
DC Output : 19 V with max. 1.58 A current

OS Support Windows® 10 86x64
Windows® 8.1 86x64
Windows® 8 , 32bit/64bit
Windows® 7 , 32bit/64bit
Windows® Vista , 32bit/64bit
Windows® XP , 32bit/64bit
Mac OS X
Linux

Dimensions 8.14 x 5.85 x 1.39 inch (WxDxH) ~ inch

Weight

Package Content RT-N66R Wireless router
Stand
RJ-45 Cable
Power Adapter
Warranty Card
Quick Start Guide

Operation mode Wireless router mode
Range extender mode
Access point mode
Media bridge mode

- All specifications are subject to change without notice. Please check with your supplier for exact offers. Products may vary.
- PCB color and bundled software versions are subject to change without notice.
- Brand and product names mentioned are trademarks of their respective companies.
- Actual data throughput and WiFi coverage will vary from network conditions and environmental factors, including network congestion, interference, and distance from the router.
- Quoted network speeds and bandwidth based on current IEEE 802.11ac specifications. Actual performance may be lower than the quoted performance. For best results, use 802.11ac-compatible devices.

Want More?

Who We Are

Chat With Us

Need Help?

Community

United States / English

[Terms of Use Notice](#) | [Privacy Policy](#) | ©ASUSTeK Computer Inc. All rights reserved.

[Chat With Us](#)