

Brown PVC Insulated Hook-Up Wire 20 AWG



Product Construction

20 AWG (10X30) Tinned Copper Wire

Conductor

20 AWG (10X30) Tinned Copper Wire Conductor per ASTM B-33

Insulation

Colour coded PVC

Temperature : -40°C to +105°C

Voltage Rating : 300 volts

Specifications

Gauge : 20 AWG

Strands : (10X30) Tin Copper Wire

Nominal Insulation Wall : 0.016 in.

Insulation Type : PVC

Nominal O.D. : 0.07 in.

Insulation Temperature : -40°C to +105°C

Voltage Rating : 300 V

Other Information

Approvals : RoHS Compliant

Part Number Table

Description	Part Number
Brown PVC Insulated Hook-Up Wire, 20 AWG	24-15081