

RJ45 Patch Cord Cat5e UTP

Right Angle Plug to Straight Plug


multicompPRO

**RoHS
Compliant**



Specifications

Standard	: ISO/IEC11801, TIA-568-C.2
Sheath Material	: PVC
External O.D.	: 5.5mm \pm 0.4mm
Connector	: RJ45 8P8C Gold Plating 3 μ "
Conductor Material	: Stranded-Bare Copper
Conductor Nom. O.D.(mm)	: 24AWG(7/0.20)

Diagram



Wire Diagram



Part Number Table

Description	Length	Part Number
RJ45 Patch Cord Cat5e UTP, 24AWG/7	10 feet	MPC0001

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/exclusive-brands
Farnell.com/exclusive-brands
Element14.com/exclusive-brands

multicompPRO