

NOTES:

1. MATERIAL

1.1 HDMI CABLE: [(7/0.10BC*1P+7/0.10BC+AM)*5PCS+7/0.10BC*4C+AM
+7/0.12BC+128/0.12ALM++BLACK PVC JACKET.

OD: 6.0 ± 0.2 MM

CABLE MARKING: E324703 AWM STYLE 20276 80°C 30V HIGH SPEED
HDMI® CABLE WITH ETHERNET

1.2 HDMI TYPE A MALE: BLACK INSULATION,
GOLD PLATED CONTACTS, GOLD PLATED SHELL

1.3 ALL HOOD: MOLDED BLACK PVC AND U ZINC ALLOY SHELL ASSEMBLY (SILVER).


2. ELECTRICAL

- 2.1 100% OPEN AND SHORT TEST.
- 2.2 CONDUCTOR RESISTANCE: 5 OHMS MAX.
- 2.3 INSULATION RESISTANCE: 10 MEGOHMS MIN.
- 2.4 HI-POT: DC300V/0.01S.
- 2.5 HDTV-DVD TEST : 1080P.

3. PACKAGING: A PC/PE-BAG PACKAGING.

4. ALL MATERIALS ARE REACH COMPLIANT.

PIN OUT



CUSTOMER	L
AV22522	500 ± 30mm
AV22523	1000 ± 30mm
AV22524	1500 ± 50mm
AV22525	2000 ± 50mm
AV22526	3000 ± 70mm
AV22527	5000 ± 70mm

LENGTH TOLERANCE: X. ± 0.5 .X ± 0.2 .XX ± 0.1	SCALE: FREE	CUS. NAME: CPC	ENG:		
ANGLE TOLERANCE: X° ± 3° .X° ± 1°	UNIT: mm		PRODUCT NO: N/A	CUSTOMER NO: P/N	CHECKED:
VERSION: 00	PAGE: 1/1	DRAWING NO: HF2735	PRODUCT DESCRIPTION: HDMI AM/AM		APPROVED:

00	NEW ISSUE	2019-04-25
REV.	MODIFY DESCRIPTION	DATE