

## GC-PM 46/3 S

#### **Petrol Lawn Mower**

Item No.: 3400727

Ident No.: 11016

Bar Code: 4006825617931

The GC-PM 46/3 S petrol lawn mower is a robust, very efficient and indispensable helper for the mowing of extensive lawns. Its powerful one-cylinder four-stroke engine generates a high torque for quickly coping with even dense, high growth. A disengageable rear-wheel drive ensures continuous progress and makes it easier to mow in difficult terrain. For individual selection of the cutting height there is a central 7-level cutting height adjustment facility.

#### **Features**

- 4-stroke Einhell OHV engine with 1 cylinder
- Disengageable rear-wheel drive
- Central cutting height adjustment, 7 levels
- Ergonomic folding handle
- Attractive, powder-coated sheet steel housing
- Hard-wearing large-capacity textile grass bag
- Handle with starter cable
- Recommended for lawn areas up to 1.400 m²

### **Technical Data**

- Engine four-stroke, air cooled

Engine displacement 135 cm³
Power 2 kW
Working speed 2900 min^-1
Capacity of fuel tank 1.3 L
Cutting width 46 cm

- Cutting height adjustment 7 settings | 30-70 mm |

central

Capacity of catch bag
Wheel diameter front
Wheel diameter rear
210 mm

## Logistic Data

- Product weight 31.3 kg- Gross weight single packaging 35.3 kg

- Dimensions single packaging 790 x 575 x 443 mm

- Pieces per export carton 1 Pieces

- Dimensions export carton 790 x 570 x 440 mm - Container quantity (20"/40"/40"HC) 140 | 299 | 360















# Available as special accessories

spare blade BG-PM 46 / 46 S Accessory Garden Technique Item No.: 3405529 Bar Code: 4006825548884 Einhell Grey