

Tool set mechanic



screwdriver, diagonal cutters, combination pliers, 5-pcs. in bag

Z 99 0 006 02

Order-No.	
30824	1
⊖	Screwdriver SoftFinish® Slotted with round blade for low-lying screws 3,5 x 100 (00691) / 5,5 x 125 (00698)
⊕	Screwdriver SoftFinish® Phillips with round blade PH2 x 100 (00759)
	Combination pliers Industrial with DynamicJoint® and OptiGrip with extra long cutting edge 180mm, 7" (30826)
	Diagonal cutters Industrial with DynamicJoint® With Wiha DynamicJoint®. 160mm, 6 1/2" (30827)

Tool set operator kit ESD



5-pcs. in bag

9300-015

Order-No.	
33504	1
⊖	Screwdriver Precision ESD Slotted 2,5 x 50 (07636)
⊕	Screwdriver Precision ESD Phillips PH0 x 50 (07641)
	Universal tweezers Professional ESD Type AA 130mm, AA (32318)
	SMD belt shears (31989)
	Dust and dirt brush x (39141)

Tool set ESD



Pliers, screwdriver, tweezers, 9-pcs. in bag

9300-016

Order-No.	
33505	1
⊖	Screwdriver Precision ESD Slotted 2,0 x 40 (07635) / 2,5 x 50 (07636)
⊕	Screwdriver Precision ESD Phillips PH00 x 40 (07640) / PH0 x 50 (07641)
⊛	Screwdriver Precision ESD TORX® T5 x 40 (07659) / T6 x 40 (07660)
●	Needle nose pliers Professional ESD straight 120mm, 4 3/4" (26799)
	Diagonal cutters Professional ESD wide, pointed head without bevelled edge 115mm, 4 1/2" (26821)
	Universal tweezers Professional ESD Type AA 130mm, AA (32318)

INFOBOX:
**Electrostatic
conductive ESD
tools**



Sensitive, electronic components can be damaged even at a very low voltage.

- Dissipative tools by Wiha discharge the electrostatic energy in a controlled, safe manner.
- ESD tools meet the ESD Standard IEC 61340-5-1.
- ESD tool handles have a surface resistance of 10⁶ - 10⁹ Ohm.