



Main

Range compatibility	Harmony XVM Optimum
Accessory / separate part category	Lighting accessory
Accessory / separate part type	Super bright LED
Accessory / separate part destination	Beacon and indicator bank
Bulb base	BA 15d
Signalling type	Steady
Signalling colour	Orange
[Us] rated supply voltage	24 V AC/DC
Luminance	900 cd/m ²
Sale per indivisible quantity	1

Complementary

Product weight	0.009 kg
----------------	----------

Environment

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1529 - Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.