

Screwdriver SoftFinish®



⊖ Slotted with one-piece hexagonal blade and solid steel cap

530

Order-No.	⊖	↔	⊖	⬢	⊖	mm	📦
03223	3,5	75	0,6	4.0	-	186	10
03224	4,5•	90	0,8	4.0	-	201	10
03225	5,5	100	1,0	5.0	8	213	10
03226	6,5	125	1,2	6.0	10	238	10
03228	8,0	150	1,2	8.0	13	271	5
03230	10,0	175	1,6	8.0	13	296	5
03231	12,0	200	2,0	10.0	16	321	5
03232	14,0•	250	2,5	10.0	16	371	5

• Additional dimension. Non-DIN size.

⊕ Phillips with one-piece hexagonal blade and solid steel cap

531

Order-No.	⊕	↔	⬢	⊖	mm	↔	📦
03237	PH1	80	5,0	8	186	30	10
03238	PH2	100	6,0	10	213	36	10
03239	PH3	150	8,0	13	268	41	10

⊕ Pozidriv with one-piece hexagonal blade and solid steel cap

532

Order-No.	⊕	↔	⬢	⊖	mm	↔	📦
03245	PZ1	80	5,0	8	186	30	10
03246	PZ2	100	6,0	10	213	36	10
03247	PZ3	150	8,0	13	268	41	10

Screwdriver SoftFinish®



⊖ Slotted with round blade and lasered mm scale

3021

Order-No.	⊖	↔	⊖	●	mm	↔	📦
36085	4,0	100	0,8	4.0	211	30	10
35397	5,5	125	1,0	5.5	236	30	10

DIN ISO 2380.

⊕ Phillips with round blade and lasered mm scale

3111

Order-No.	⊕	↔	●	mm	↔	Scale	📦
36072	PH1	80	4,5	191	30	20-70	10
35398	PH2	100	6,0	218	36	20-90	10

DIN ISO 8764-PH.

⊕ Pozidriv with round blade and lasered mm scale

3131

Order-No.	⊕	↔	●	mm	↔	Scale	📦
36073	PZ1	80	4,5	191	30	20-70	10
35399	PZ2	100	6,0	218	36	20-90	10

DIN ISO 8764-PZ.

Screwdriver SoftFinish®



⊖ Slotted with fixing function

398

Order-No.	⊖	↔	⊖	mm	↔	📦
32867	2,5	75	0,4	186	30	5
32868	3,0	100	0,5	211	30	5
32869	4,0	125	0,8	243	36	5
32870	5,0	150	1,0	268	36	5
32871	6,0	175	1,2	293	36	5

⊕ Phillips with fixing function

397

Order-No.	⊕	↔	mm	↔	📦
32406	PH0	100	211	30	5
32404	PH1	125	236	36	5
32405	PH2	175	286	36	5