



Main

Product or component type	Network braking unit
Range compatibility	Altivar 71
[Us] rated supply voltage	400 V
Maximum current Irms	65 A AC 78 A DC
Permanent braking power	26 kW
Maximum braking power	45 kW

Complementary

Supply circuit type	AC
Associated fuse rating	100 A at 690 V
Supply voltage limits	380...415 V
Network frequency	40...60 Hz +/- 10 %
Overload protection	1.2 x maximum current
Efficiency	97 %
Cos phi	1
Electrical connection	Bare wires connection M6 35 mm ² connection capacity
Height	580 mm
Width	270 mm
Depth	295 mm
Product weight	32 kg

Environment

IP degree of protection	IP20
relative humidity	Class F without condensation 5...85 %
ambient air temperature for operation	> 40...< 55 °C with current derating 3 % per °C 5...40 °C without current derating
ambient air temperature for storage	-25...55 °C
operating altitude	<= 1000 m without current derating

Contractual warranty

Warranty period	18 months
-----------------	-----------