

**ZA2BG2**  
key selector switch head - 2 pos. - stay put -  
withdrawal left-hand position



Main

Range of product	Harmony XAC
Product or component type	Selector switch
Component name	ZA2
Product compatibility	XACA

Complementary

Marking	Unmarked
Cap/operator or lens colour	Black
Mounting location	Front of enclosure Base of enclosure
Sale per indivisible quantity	1
Product weight	0.042 kg

Environment

standards	EN/IEC 60204-32 EN/IEC 60947-5-1 UL 508 CSA C22.2 No 14
ambient air temperature for operation	-25...70 °C
ambient air temperature for storage	-40...70 °C
vibration resistance	15 gn (f = 10...500 Hz) conforming to IEC 60068-2-6
shock resistance	100 gn conforming to IEC 60068-2-27
overvoltage category	Class II conforming to IEC 61140
IP degree of protection	IP65 conforming to IEC 60529
IK degree of protection	IK08 conforming to EN 50102

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.