


## XAPG59505

die-cast empty control station - XAP-G - Ø22 - 5 cut-outs



### Main

Range of product	Harmony XAP
Product or component type	Die-cast empty control station
Device short name	XAPG
Product destination	For Ø 22 mm control and signalling units
Number of cut-out	5 cut-outs
Colour of base of enclosure	Grey RAL 7032
Colour of cover	Grey RAL 7032
Material	Zinc alloy
Cable entry	1 hole with blanking plug for cable gland with <= 14 mm 1 hole without blanking plug for cable gland with <= 14 mm
Product mounting	Flush mounting
IP degree of protection	IP65 conforming to IEC 60529 IP657 conforming to NF C 20-010

### Complementary

Number of vertical rows	1
-------------------------	---

### Environment

protective treatment	TC
ambient air temperature for storage	-40...70 °C
ambient air temperature for operation	-25...70 °C
electrical shock protection class	Class I conforming to IEC 60536 Class I conforming to NF C 20-030

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.