

## XACB9115

booted head for pushbutton XAC-B - yellow - 4 mm, -  
25...+70 °C



### Main

Range of product	Harmony XAC
Product or component type	Head for push-button
Component name	XACB
Marking	Unmarked
Operator additional information	Booted
Operating travel	4 mm
Cap/operator or lens colour	Yellow
Product compatibility	XENB.... XENC.... XEND.... XESB2011 XESD2201 XESD2241 XESD2251
Sale per indivisible quantity	10

### Complementary

Product weight	0.005 kg
----------------	----------

### Environment

standards	EN 60947-5-1 IEC 60947-5-1 CSA C22.2 No 14
ambient air temperature for operation	-25...70 °C
ambient air temperature for storage	-40...70 °C
vibration resistance	15 gn (f = 10...500 Hz) conforming to IEC 60068-2-6
shock resistance	100 gn conforming to IEC 60068-2-27
electrical shock protection class	Class II conforming to IEC 61140
IP degree of protection	IP65 conforming to IEC 60529
IK degree of protection	IK08 conforming to EN 50102

### Contractual warranty

Warranty period	18 months
-----------------	-----------