

XACB9122

booted head for pushbutton XAC-B - black - 4 mm, -40...+70 °C



Main

Range of product	Harmony XAC
Product or component type	Head for push-button
Component name	XACB
Marking	Unmarked
Operator additional information	Booted
Operating travel	4 mm
Cap/operator or lens colour	Black
Product compatibility	XENB.... XENC.... XEND.... XESB2011 XESD2201 XESD2241 XESD2251
Sale per indivisible quantity	10

Complementary

Product weight	0.005 kg
----------------	----------

Environment

standards	EN 60947-5-1 IEC 60947-5-1 CSA C22.2 No 14
ambient air temperature for operation	-40...70 °C
ambient air temperature for storage	-40...70 °C
vibration resistance	15 gn (f = 10...500 Hz) conforming to IEC 60068-2-6
shock resistance	100 gn conforming to IEC 60068-2-27
electrical shock protection class	Class II conforming to IEC 61140
IP degree of protection	IP65 conforming to IEC 60529
IK degree of protection	IK08 conforming to EN 50102

Contractual warranty

Warranty period	18 months
-----------------	-----------