



### Main

|                             |                                                                                                     |
|-----------------------------|-----------------------------------------------------------------------------------------------------|
| Range of product            | 9007                                                                                                |
| Series name                 | Severe duty                                                                                         |
| Product or component type   | Limit switch lever                                                                                  |
| Device short name           | 9007T/FT                                                                                            |
| Associated head             | 9007AS9<br>9007BS9<br>9007CS9<br>9007NS9<br>9007T10S9<br>9007T5S9                                   |
| Associated complete product | 9007T<br>9007FT<br>9007C...S9                                                                       |
| Movement of operating head  | Rotary                                                                                              |
| Type of operator            | Cast zinc spring return roller lever length: 2.5 in - offset: - convertible rollers, 2 on same side |
| Type of roller              | 2 steel outside roller (convertible) diameter: 1 in - width: 0.25 in                                |
| Type of approach            | Lateral approach                                                                                    |
| Positive opening            | Without                                                                                             |

### Complementary

|                  |            |
|------------------|------------|
| Switch actuation | By 30° cam |
| Product weight   | 0.1 lb(US) |

### Environment

|                                       |                      |
|---------------------------------------|----------------------|
| ambient air temperature for operation | -10...185 °F         |
| ambient air temperature for storage   | -10...185 °F         |
| environmental characteristic          | Standard environment |

### Offer Sustainability

|                                  |                                                   |
|----------------------------------|---------------------------------------------------|
| Sustainable offer status         | Not Green Premium product                         |
| RoHS (date code: YYWW)           | Will not be Compliant                             |
| REACH                            | Reference not containing SVHC above the threshold |
| Product environmental profile    | Available                                         |
| Product end of life instructions | Need no specific recycling operations             |

### Contractual warranty

|                 |           |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|