



Main

Range of product	9007
Series name	Severe duty
Product or component type	Limit switch lever
Device short name	9007T/FT
Associated head	9007AS9 9007BS9 9007CS9 9007NS9 9007T10S9 9007T5S9
Associated complete product	9007T 9007FT 9007C...S9
Movement of operating head	Rotary
Type of operator	Cast zinc spring return rod lever without rod - offset: - clamp for use with 3/16" diameter rod (not supplied)
Type of approach	Lateral approach
Positive opening	Without

Complementary

Switch actuation	By any moving part
Product weight	0.1 lb(US)

Environment

ambient air temperature for operation	-10...185 °F
ambient air temperature for storage	-10...185 °F
environmental characteristic	Standard environment

Offer Sustainability

Sustainable offer status	Not Green Premium product
RoHS (date code: YYWW)	Will not be Compliant
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.