

## ZCY71

limit switch lever ZCY - forked arm with rollers 1 track



### Main

Range of product	OsiSense XC
Series name	Standard format
Product or component type	Limit switch lever
Device short name	ZCY
Product compatibility	XCKD XCKP XCKT XCMD
Associated head	ZCE09
Movement of operating head	Rotary
Type of operator	Stay put forked arm with rollers stay put (1 track)
Tracks	28 mm for XCMD 32 mm for XCKD 32 mm for XCKP 32 mm for XCKT
Type of approach	Lateral approach

### Complementary

Switch actuation	By specific cam
Positive opening	Without

### Environment

ambient air temperature for operation	-25...70 °C
ambient air temperature for storage	-40...70 °C
environmental characteristic	Standard environment

### Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1001 - Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

### Contractual warranty

Warranty period	18 months
-----------------	-----------

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.