



Main

Range of product	Harmony XVD Optimum
Product or component type	Complete miniature beacon
Beacon or indicator bank unit type	Base unit with direct fixing mode Illuminated unit
Signalling type	Steady
Mounting diameter	45 mm
Component name	XVDLS
Material	Glass reinforced polyamide (base unit) Polycarbonate (illuminated unit)
Light source	Green bulb not included
Bulb type	Incandescent with BA 15d
[Us] rated supply voltage	<= 230 V
Power dissipation in W	< 5 W

Complementary

Connections - terminals	Screw clamp terminals, connection capacity: <= 1 x 1.5 mm ² with cable end
Cable entry	1 entry tapped for Pg 7
[Ui] rated insulation voltage	250 V conforming to IEC 60947-1
[Uimp] rated impulse withstand voltage	4 kV conforming to IEC 60947-1
CAD overall width	45 mm
CAD overall height	104 mm
CAD overall depth	45 mm
Terminals description ISO n°1	(COM-1)PW (GND)GROUND
Product weight	0.08 kg

Environment


product certifications	CSA UL
standards	EN/IEC 60947-5-1
protective treatment	TC
ambient air temperature for operation	-25...70 °C
ambient air temperature for storage	-40...70 °C
electrical shock protection class	Class II conforming to IEC 60536
IP degree of protection	IP40 conforming to IEC 60529

Contractual warranty

Warranty period	18 months
-----------------	-----------

Illuminated Beacon

Dimensions



Illuminated Beacon

Panel Cut-out for Direct Fixing

