

L-key with T-handle



Hexagon MagicRing® brilliant nickel-plated

334R

Order-No.	●	⊚	⊚	⊚	⊚	⊚	⊚
22168	3	100	126	80	26		10
22170	4	150	176	80	26		10
22172	5	150	182	100	32		10
22174	6	150	182	100	32		10
21960	8	200	232	100	32		10
21962	10	200	238	120	38		10

L-key with T-handle



Hexagonal ball end brilliant nickel-plated

540

Order-No.	●	⊚	⊚	⊚	⊚	⊚	⊚
04111	4	150	176	80	26		10
04108	5	150	182	100	32		10
04105	6	150	182	100	32		10
04099	8	200	238	100	32		10
04096	10	200	238	120	38		10

L-key with T-handle



Hexagon brilliant nickel-plated

334

Order-No.	●	⊚	⊚	⊚	⊚	⊚	⊚
00904	2	100	-	126	80	26	10
00905	2	200	-	226	80	26	10
00906	2,5	100	-	126	80	26	10
00907	2,5	200	-	226	80	26	10
00908	3	100	-	126	80	26	10
00909	3	150	-	176	80	26	10
00910	3	200	-	226	80	26	10
00911	3•	350	5+	382	100	32	10
00912	4	100	-	126	80	26	10
00913	4	150	-	176	80	26	10
00914	4	200	-	226	80	26	10
00915	4•	350	5+	382	100	32	10
00916	5	100	-	132	100	32	10
00917	5	150	-	182	100	32	10
00918	5	200	-	232	100	32	10
00919	5	350	-	382	100	32	10
00921	6	100	-	132	100	32	10
00922	6	150	-	182	100	32	10
00923	6	200	-	232	100	32	10
00924	6	350	-	382	100	32	10
00926	7	200	-	232	100	32	10
00928	8	100	-	132	100	32	10
00929	8	150	-	182	100	32	10
00930	8	200	-	232	100	32	10
00931	8	350	-	382	100	32	10
00933	10	100	-	138	120	38	10
00934	10	200	-	238	120	38	10
00937	12	200	-	238	120	38	5

• Overlength with reinforced blade.