



## Main

Range of product	OsiSense XC
Series name	Standard format
Product or component type	Limit switch lever
Device short name	ZCKY
Product compatibility	XCKL XCKM XCKS
Associated head	ZCKD05
Movement of operating head	Rotary
Type of operator	Rod lever spring return metal (square rod 3 mm, L = 125 mm)
Type of approach	Lateral approach

## Complementary

Switch actuation	By any moving part
Positive opening	Without

## Environment

Ambient air temperature for operation	-25...70 °C for standard environment
Ambient air temperature for storage	-40...70 °C for standard environment
Environmental characteristic	Standard environment

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1440 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>

---

Product end of life instructions	Need no specific recycling operations
----------------------------------	---------------------------------------

---

**Contractual warranty**

---

Warranty period	18 months
-----------------	-----------

---