



Coliseum Mini Installation Series

WM5T/70

Overview

Looking for a way to hide speakers in a room? Don't have space to put a speaker? The Coliseum WM5T/70 in-wall, flush mount loudspeaker is your answer. This compact speaker is ideally suited for many applications: commercial installations, home theatre, or home stereo. Using the volume between wall studs as an enclosure, this bass reflex speaker has a 5" woofer and mylar dome tweeter that provide impressive bass, and clean, crisp high frequency response. Installation is a snap with the provided cutting/painting template, while press-fit grille hides all mounting holes to give the WM5T/70 a very clean and finished look. All mounting hardware is also provided. The baffle is made of white ABS plastic with a matching, white, perforated metal grille. It can be easily painted to match its surroundings.

The WM5T/70 features built in 70-volt taps at 5, 10 or 20 watts as well as optional 8-ohm (25 watt) operation mean the WM5T/70's can be driven by virtually any amplification or paging system including the Coliseum CA1 or CA1T.



Features

- High Performance Two-Way In-wall Speaker
- 5-inch Woofer / 1-inch Mylar Dome Tweeter
- Selectable 70-volt or 8-ohm Operation
- Power Taps at 5, 10 and 20 Watts
- 50 watts (8-ohm mode)
- Open Back Design
- Mounting Hardware Included
- Paintable Metal Grille and ABS Plastic Baffle



Coliseum Mini Installation Series

WM5T/70

Specifications

System Type	2-way, Full Range, In-Wall Mount
Active or Passive	Passive
Program Power (Watts)	50
Nominal Impedance (Ohms)	4
Sensitivity (dB @1Watt/1m)	92
Frequency Response (Hz +/- 3dB)	80 -18,000
Driver Configuration	Tweeter, 5 inch
HF Driver(s)	Mylar Tweeter
HF Dispersion (°H x °V)	90x90
LF Driver(s)	5 inch
Inputs	Solder Lug
Other Controls / Features	Optional LT-70V5W five watt, 70V matching transformer is available
Included Hardware	Mounting Screws and Bracket
Enclosure Materials	Injection Molded, ABS Plastic
Grille	Perforated Steel
Covering / Finish	Low Reflective White
Other Details	Cutting/Painting Template and Putty Sealer Strip also included
Dimensions (DWH xbackW, inches)	3.5 x 7.5 x 11
Dimensions (DWH xbackW, cm)	9 x 19 x 28
Weight (lbs/kg)	3 / 1.4

Specifications subject to change without notice