



Coliseum C110

5-inch Mini Series Speaker

Features:

- ▷ 40 Watt Mini Series Speaker
- ▷ 90° x 90° HF Driver
- ▷ 5-inch Woofer with Tweeter
- ▷ Cabinet Is Available In Either a White (C110W) or Black (C110) Finish
- ▷ 85 to 19,000 Hz Frequency Response
- ▷ 70-volt 'Matching Transformer'
- ▷ Binding Post and 1/4" Phone Connectors
- ▷ Injection Molded, ABS Plastic Cabinet Construction
- ▷ Two-year Unconditional Warranty*

*Warranty valid in Canada and the United States only



Overview:

The Coliseum C110 is a high quality, weather resistant speaker which features specially treated drivers in a rugged plastic enclosure. It is well-suited for many applications including commercial installations, home theaters, home stereos, reference monitors and personal stage monitors. The C110 is a bass reflex enclosure with a tuned port and a 5-inch woofer whose computer-optimized design gives improved bass performance over conventional 5-inch woofer enclosures. With a power rating of 40 watts of continuous music power the C110 is accurate from 85Hz to 19kHz with an efficiency of 92dB.

The C110 features an internal 70-volt 'matching transformer' which allows multiple C110s to be connected together without danger of overloading the power amplifier due to impedance drop. The user has a choice of three sensitivity settings (10w, 20w, 30w or off) selected via a rotary switch located on the rear panel of the speaker, allowing convenient adjustment of the relative volumes of multiple interconnected cabinets.

A wide variety of mounting options are available using the four integral screw-slots or the provided metal L-bracket which allows it to be angled up, down or sideways depending on the mounting orientation. The C110 is available in a low-reflectance black or white finish with a matching, perforated metal grille and can be painted to match its surroundings.

C110 Specifications:

| Model | C110 |
|---------------------------|--------------------------------------|
| TYPE | 2-Way, Tuned Port |
| SYSTEM | Bass Reflex |
| PROGRAM POWER (watts) | 40 |
| IMPEDANCE (ohms) | 70V Transformer / Passive 8Ω |
| SENSITIVITY (dB @ 1W/1m) | 92 |
| FREQ. RESP. (+/-3dB) | 85 - 19k |
| WOOFER | 5" |
| TWEETER | Mylar |
| INPUTS | Screw Terminals |
| CABINET CONSTRUCTION | Injection Molded ABS Plastic |
| STANDARD COLOR | Black |
| OPTIONAL COLOR | White (C110W) |
| STANDARD HARDWARE | Rear Key Hole Mounts (4) / L-Bracket |
| OPTIONAL HARDWARE | - |
| 70V TRANSFORMER TAPS | 10W / 20W / 30W / 8R |
| DIMENSIONS (DxWxH inches) | 5.5 x 6.26 x 8.9 |
| DIMENSIONS (DxWxH cm) | 14 x 15.9 x 22.6 |
| WEIGHT (lbs / kg) | 3.8 / 1.7 |

