

## Han M23 Metal Screw Cover – Chain 100mm



Part number	09 15 100 9103
Specification	Han M23 Metal Screw Cover – Chain 100mm
HARTING eCatalogue	<a href="https://b2b.harting.com/09151009103">https://b2b.harting.com/09151009103</a>

### Identification

Category	Hoods/Housings
Series of hoods/housings	Han <sup>®</sup> M23 Signal
Type of hood/housing	Cover
Description of hood/housing	for hoods With chain (100 mm)

### Version

Locking type	Screw locking
Size	M23
Details	Not compatible to ComLock

### Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP67 in locked position IP69 / IPX9K acc. to ISO 20653 in locked position

### Material properties

Material (hood/housing)	Copper-zinc alloy
Surface (hood/housing)	Nickel plated
RoHS	compliant with exemption
RoHS exemptions	6c: Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Lead



Pushing Performance

## Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076
----------	-----------------------

## Commercial data

Packaging size	5
Net weight	26.8 g
Country of origin	Germany
European customs tariff number	85389099