



Energizer® Vision HD Focus Rechargeable Metal

NEW! Part Number ENPMHRL7

The Energizer® Vision HD Rechargeable Metal Light delivers high-performance innovation with exceptional light output. It is easy to use and features USB-in and out ports, which means it is rechargeable and can also charge devices making it a great option for situations when you need to charge your device. This light is built with durable aircraft grade aluminum which makes it a great tool for DIY projects and work tasks. The unique MAXVIZ technology enables users to experience sharp high-definition performance with daylight color and wide uniform light output. Its brightness, durability and features make the Energizer® Vision HD Rechargeable Metal Light a dependable light for various tasks.

Design Benefits

- ✓ **Patented One Press Digital Focusing** allows users to broaden or narrow the beam between spot and flood light
- ✓ **Rechargeable** USB Port In
- ✓ **USB Port Out:** Charges Devices
- ✓ 15-20 Year Design To Last based on typical consumer usage patterns
- ✓ Durable Aircraft Grade Aluminum


Performance Benefits

- ✓ **MAXVIZ Technology** to deliver a wide, powerful beam and high-definition vision
- ✓ Exceptional light output for any task
- ✓ Up to 15X Brighter than Standard LED Technology
- ✓ Fully Charge in 8 hours*

Light and Power Source

- ✓ Features LED technology
- ✓ Rechargeable Lithium Ion Battery (26650) – Non Removable

*Light must be turned off while charging.



7 Operating Modes					
Mode	Lumens	Runtime	Beam Distance	Impact Resistant	Water Resistant
High	1000	4hrs	200m	1m	IPX4
Low	250	8hrs	-	1m	IPX4
Strobe	-	-	-	1m	IPX4
Spot High	Digital Focus				
Spot Low					
Wide High					
Wide Low					