



## ES5160L.CR.BGS

High precision Ergo-tek Slim Cutters - Extra Large Rounded Oval head, semi-flush. OAL: 125 mm. ESD safe



Extremely strong and durable with rounded head, for intensive cutting operations

*High precision Cutters & Pliers leaflet*

### Documents

Grip handle material TDS

### Product Details

Market - MEDICAL DEVICE	yes
Market - LIFE SCIENCE & MICROSCOPY	yes
Market - ELECTRONICS	yes
Market - WATCHMAKING & JEWELRY	yes
Category	High Precision Cutters
Kit	no
ESD safe	yes
Body material	100Cr6
Grip handle material	Ergo-tek Slim - TPE + PP

<b>Head shape</b>	Oval
<b>Head width (mm - in) - C</b>	16.00 - 0.63
<b>Size/type</b>	Extra Large Rounded
<b>Cutting edges</b>	Semi-Flush
<b>OAL (mm - in) - A</b>	125.00 - 4.921
<b>B (mm - in)</b>	14.00 - 0.551
<b>Head thickness (mm - in) - D</b>	6.40 - 0.252
<b>F (mm - in)</b>	0.50 - 0.02
<b>Cutting capacity soft (mm)</b>	0.5-3
<b>Cutting capacity soft (AWG)</b>	24-09
<b>Cutting capacity medium (mm)</b>	0.4-2.5
<b>Cutting capacity medium (AWG)</b>	26-10
<b>Cutting capacity hard (mm)</b>	0.06-1.1
<b>Cutting capacity hard (AWG)</b>	42-17
<b>RoHS compliant</b>	yes



© 2019 IDEAL-TEK SA

via Giuseppe Motta 4, 6828 Balerna - Switzerland

T +41 91 683 32 29 - F +41 91 683 03 71 - E info@ideal-tek.com