



ES5246.CR.BG

High precision Ergo-tek Slim Cutters - Small Oblique head, flush. OAL: 125 mm. ESD saf



Angulated cutter to maximize accessibility and visibility when limited space.

High precision Cutters & Pliers leaflet

Documents

 Grip handle material TDS

Product Details

Market - MEDICAL DEVICE	yes
Market - LIFE SCIENCE & MICROSCOPY	yes
Market - ELECTRONICS	yes
Market - WATCHMAKING & JEWELRY	yes
Category	High Precision Cutters
Kit	no
ESD safe	yes
Body material	100Cr6
Grip handle material	Ergo-tek Slim - TPE + PP
Head shape	Oblique

Head width (mm - in) - C	10.00 - 0.394
Size/type	Small
Cutting edges	Flush
OAL (mm - in) - A	125.00 - 4.921
B (mm - in)	17.00 - 0.669
Head thickness (mm - in) - D	6.40 - 0.252
G (mm - in)	4.00 - 0.157
Cutting capacity soft (mm)	0.1-1.2
Cutting capacity soft (AWG)	38-17
Cutting capacity medium (mm)	0.1-0.4
Cutting capacity medium (AWG)	38-26
Net weight (g-lb)	84 - 0.185
RoHS compliant	yes



© 2019 IDEAL-TEK SA

via Giuseppe Motta 4, 6828 Balerna - Switzerland
T +41 91 683 32 29 - F +41 91 683 03 71 - E info@ideal-tek.com