



ES5247.CR.BG

High precision Ergo-tek Slim Cutters - Oblique head, full-flush. OAL: 125 mm. ESD safe



Angulated cutter to maximize accessibility and visibility when limited space.

High precision Cutters & Pliers leaflet

Documents

Grip handle material TDS

Product Details

Market - MEDICAL DEVICE	yes
Market - LIFE SCIENCE & MICROSCOPY	yes
Market - ELECTRONICS	yes
Market - WATCHMAKING & JEWELRY	yes
Category	High Precision Cutters
Kit	no
ESD safe	yes
Body material	100Cr6
Grip handle material	Ergo-tek Slim - TPE + PP

Head shape	Oblique
Head width (mm - in) - C	10.00 - 0.394
Size/type	Small
Cutting edges	Full-Flush
OAL (mm - in) - A	125.00 - 4.921
B (mm - in)	17.00 - 0.669
Head thickness (mm - in) - D	6.40 - 0.252
G (mm - in)	8.00 - 0.315
Cutting capacity soft (mm)	0.1-1.2
Cutting capacity soft (AWG)	38-17
Cutting capacity medium (mm)	0.1-0.6
Cutting capacity medium (AWG)	38-23
Net weight (g-lb)	86 - 0.19
RoHS compliant	yes



© 2019 IDEAL-TEK SA

via Giuseppe Motta 4, 6828 Balerna - Switzerland

T +41 91 683 32 29 - F +41 91 683 03 71 - E info@ideal-tek.com