



## TE-VC 1930 SA; Ex; UK

Wet/Dry Vacuum Cleaner (elect)

Item No.: 2342195

Ident No.: 11013

Bar Code: 4006825599305

The TE-VC 1930 SA wet and dry vacuum cleaner is an indispensable helper which provides good service to the ambitious DIY enthusiast on cleaning jobs in the home, workshop and garage. Its stainless steel tank has a capacity of 30 liters for devouring both dirt and liquids, with a drain screw provided for the user-friendly and clean disposal of the vacuumed liquid. A practical blow connector is also provided. An integrated socket with automatic function and delayed switch-off enables this cleaner to be used as a vacuum extraction system for electric tools.

### Features

- 30 l tank made of stainless steel
- 2 large wheels, 2 castors
- Carry handle and cable holder
- Integrated appliance socket with automatic function and switch-off delay
- Blow connector
- Water drain screw
- Accessory mount
- 3-piece plastic suction pipe
- 1 suction hose 36 mm
- Large suction nozzle with combination insert for wet and dry vacuuming of floors
- Crevice nozzle
- 1 pleated filter
- 1 foam filter for wet vacuuming

### Technical Data

- Power	1500 W
- Max. suction power	16 kPa
- Suction hose length	250 cm
- Suction hose diameter	36 mm
- Vessel capacity	30 L
- Max. power of socket 230 V	1490 W
- Sound power level LWA	80 dB (A)
- Mains supply	230 V   50 Hz

### Logistic Data

- Product weight	3.27 kg
- Gross weight single packaging	8.63 kg
- Dimensions single packaging	400 x 390 x 550 mm
- Pieces per export carton	1 Pieces
- Gross weight export carton	8.63 kg
- Dimensions export carton	405 x 385 x 553 mm
- Container quantity (20"/40"/40"HC)	336   696   821

