

MOBILE **BLUETOOTH**[®] SPEAKER

STEEL DRUM

Mobile compact speaker for smartphones, tablets etc. via Bluetooth[®]



3
Watt

Max. Music Power

14h+

Rechargeable battery
14+ hours playback



Speakerphone mode



Bluetooth[®] 5.0

Top-Features

- ✓ wireless music playback for all Bluetooth enabled devices
- ✓ supports the remote function for music control with play/pause/title forward/title back
- ✓ battery-operated for complete mobility: the battery can be charged using a USB cable
- ✓ fast charging within 2 hours
- ✓ with anti-slip rubber ring
- ✓ line-in for optional use of the loudspeaker via a cable
- ✓ high-quality and robust aluminium housing
- ✓ integrated hands-free function (Speaker Phone Mode)
- ✓ LED indicator shows if power supply is active

Technical data

Bluetooth[®] Technology	v5.0	Charging voltage	5 V 500 mA (USB)
Bluetooth[®] Profile	A2DP V1.2; AVRCP V1.4; HFP V1.5	Connections	3.5 mm Stereo Plug Micro USB
Range	< 10 m	Size	70 x 63 x 63 mm
Max. Music Power	3W	Weight	171 g
Sound System	Mono	What's in the Box	Mobile Bluetooth [®] speaker; USB-Adapter- charging cable; Connecting cable with a 3.5 mm jack plug; User manual
Frequency	200 Hz - 20 kHz		
Impedance	4 Ohm	Compatibility	
Battery Type	3.7V Li-polymer 750 mAh, 2.775 Wh		
Playback	≤ 8 h (via Bluetooth [®]) ≤ 14 h (via AUX)		
Charging time	~ 2 h		

Available in these colors

00173178
anthracite



00173179
silver



00173180
gold



The Bluetooth word mark and logos are owned by the Bluetooth SIG, Inc. and any use of such marks by hama is under license. Other trademarks and trade names are those of their respective owners.



00
173178

All specifications and descriptions are subject to change without notice.

hama[®]

THE SMART SOLUTION