



Professional PC Labelling Machine

Desktop labelling machine with PC connection and label design software.

- Large colour graphic display with backlight
- Wide PC style keyboard
- Automatic label cutter
- Built-in editable label designs for common labelling applications
- Prints 3.5, 6, 9, 12, 18 and 24mm labels



“The large colour LCD display makes it easy to design and preview my labels before printing. An automatic cutter, easy-to-type keyboard and high speed printing plus the ability to print labels from my PC or Mac ensures I keep my office organised through clear identification of important items.”



P-touch
D600VP

The professional stand-alone and PC connectable labelling machine

The P-touch D600VP creates durable fade-proof labels by using the easy-to-use integrated labelling functions, or directly from your PC or Mac thanks to the fully-featured P-touch Editor label design software.

A large colour LCD display with label preview function, and a wide PC-style keyboard make it easy to quickly produce your labels in various colour and size combinations.

Alternatively, connect to your PC or Mac and be creative by using various fonts, text styles, images and frames on your label design. You can even link to text contained in a Microsoft Excel spreadsheet to quickly print many labels at once, thanks to its high-speed print capabilities and fully automatic cutter.



Print labels
3.5 – 24mm in width



Automatic label
cutter



Easy-to-type
PC-style keyboard



Prints labels from
your PC or Mac



High-resolution
colour display



Uses 6 x AA batteries*
or included AC adapter



Built-in editable
label designs



14 fonts ; 99 frames
Over 600 symbols

* LR6/HR6. Batteries not supplied.

P-touch laminated labels – designed to last

Brother P-touch laminated TZe tapes consist of six layers of materials, resulting in a thin yet extremely strong label. The thermal transfer ink is sandwiched between two protective layers of PET (polyester film), which protects the text against the effects of liquids, abrasion, temperature, chemicals and sunlight. As the labels have been tested to the extreme, you can be confident of a professional quality label that has been designed to last.



Laminated



Temperature
Resistant



Water
Resistant



Fade
Resistant



Abrasion
Resistant



Chemical
Resistant



Easy Peel



Strong
Adhesion

Clearly identify items with a durable P-touch label

Around the home, office, school, shop and other places of work, there are many uses for long lasting, durable P-touch labels. Common examples include:

Cables and plugs • CD's and DVD's • USB flash drives • Office equipment • File folders • Filing cabinets • Mail rooms • Staff and visitor name badges • Signage • Notice boards • Shelving • Telephone extension numbers



PT-D600VP

In the box

PT-D600 labeling machine
24mm black on white tape cassette (4m)
AC adapter
USB cable
User guide
Carry case

Main features

Display type 20 chrs x 3 lines colour LCD with print preview
PC interface Windows: USB 1.1 / 2.0 / 3.0 ; Mac: USB 1.1 / 2.0
Print speed 30mm / second
High-resolution print mode Yes (180 x 360dpi)
Maximum tape width 24mm
Maximum print height 18mm
Cutter type Automatic
Battery type 6 x AA alkaline/rechargeable batteries (LR6/HR6 - not supplied)

Label Creation

Fonts 14 fonts ; 11 styles; 6 to 48 point size
Max. lines per label 7
Max. text blocks 5
Symbols 617
Frames 99
Barcodes 9 protocols
Automatic numbering 1-99
Copy printing 1-99
Vertical text printing Yes (standard and bold)
Pre-set formats 30 templates
Easy-print graphic label function 25 pre-designed labels
Download labels from internet Yes
Cable marking function Yes

Memory

Maximum characters per label 280
Label memory locations 99 (Maximum of 2,800 characters in total across all locations)

PC Software

Supported operating systems Windows Vista®
Windows® 7
Windows® 8
Mac OS X 10.7 - 10.9
Cable labelling wizard Yes
Font faces All installed true-type fonts
Font styles 12
Image import JPG, BMP, TIFF and other popular types
Screen capture Yes
Frames 154
Barcodes 21 protocols including 1D/2D barcodes
Database connection support (Windows only) Microsoft Excel, csv, mdb, txt

Visit <http://support.brother.com> for latest software and drivers

General

Supplies
Tape type ; Tape widths TZe tape cassettes ; 3.5, 6, 9, 12, 18, 24mm
Optional accessories
AC adapter AD-E001 AC adapter
Weights & Dimensions
PT-D600 201mm(w) x 192mm(h) x 86mm(d) ; 950g

For detailed specifications and to see the full product range, please visit www.brother.co.uk

Contact:

brother
at your side

www.brother.co.uk

Brother UK Ltd, Audenshaw, Manchester M34 5JD

Tel: +44(0)333 777 4444 Fax: +44(0)161 931 2218

Web: www.brother.co.uk

All specifications correct at time of printing (July 2014). Brother is a registered trademark of Brother Industries Ltd. Brand product names are registered trademarks or trademarks of their respective companies.

Label images shown are for illustrative purposes only and some aspects may not be reproducible on this model. Product specifications may be subject to change. E&OE.

