

**THM**  
**EL 27 MM WS 30M**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com


**Customised identification: EL**

The endless variations of MultiMark markers make them an economical alternative to conventional tag rails or special labels. For any given width, the length can be precisely configured by the software to match the respective markers perfectly. A blade is used to cut the labels individually to the specified size. Perfect for producing large labels for function blocks or complete terminal blocks.

**Your benefits with MultiMark**

- Double laminated polyester
- Can be used with equipment from many manufacturers
- Device markers with a familiar design

**General ordering data**

Type	EL 27 MM WS 30M
Order No.	<a href="#">2006630000</a>
Version	THM, Device markers, 27, white
GTIN (EAN)	4050118391374
Qty.	1 pc(s).
compatible printer	<a href="#">2448870000</a> <a href="#">2430920000</a>

## Data sheet

**THM  
EL 27 MM WS 30M**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

## Technical data

### Dimensions and weights

Length	30,000 mm	Length (inches)	1,181.1 inch
Height	27 mm	Height (inches)	1.063 inch
Depth	0.1 mm	Depth (inches)	0.004 inch
Net weight	229 g		

### General data

Adhesive	Acrylate adhesive	Approval acc. to UL 969	Yes
Colour	white	Halogen	No
Length	30,000 mm	Material	Polyester
Number per roll	1	Operating temperature range	-40...120 °C
UL 94 flammability rating	V-0	Version	halogen-free, Self-adhesive

### Classifications

ETIM 6.0	EC001288	eClass 6.2	27-14-91-29
eClass 9.0	27-40-06-29	eClass 9.1	27-40-06-29

### Approvals

ROHS	Conform
------	---------

### Downloads

Engineering Data	<a href="#">EPLAN, WSCAD</a>
------------------	------------------------------

**Data sheet**

**THM  
EL 27 MM WS 30M**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**



**THM  
EL 27 MM WS 30M**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Accessories**

**Ink ribbons THM MMP**



These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

**General ordering data**

Type	Order No.	Version	GTIN (EAN)	Qty.
RIBBON MM 76/360 SW	<a href="#">2005080000</a>	Ink ribbon	4050118389951	1 pc(s).

**Accessories / replacement parts**



Our marking systems can be used to quickly and reliably label connector markers, conductor and cable markers, device markers and labels. The M-Print® PRO software enables rapid and easy identification of your electrical equipment. You can design, label and order your marking materials professionally and quickly. Frames, barcodes, graphics or photos are easily incorporated. The versatile data conversion routines enable quick and flexible data integration. The Weidmüller PrintJet ADVANCED, MCP Plus and MCP Basic printers and the THM series printers are available for printing.

**General ordering data**

Type	Order No.	Version	GTIN (EAN)	Qty.
THM MMP ROLLER 115	<a href="#">1357420000</a>		4050118160314	1 pc(s).

**THM  
EL 27 MM WS 30M**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Accessories**

**THM MMP**



**MMP**

The only printer you need for your marking tasks The THM MMP is a compact and modular thermal transfer printer that fully demonstrates its many advantages and high number of potential uses. The integrated cutting and perforation option enables continuous materials to be cut to any length – making your work considerably easier when it comes to cutting and assigning the respective labels. The printer edits markers and labels from the MultiMark family as well as continuous materials, textile and polyester labels, shrink-fit sleeves and PLC labels.

**Your benefits with MultiMark**

- One printer for all jobs
- Ideal for small and medium print volumes
- Nearly maintenance-free thanks to thermal transfer technology
- Good legibility (resolution: 300 dpi)
- Flexibility thanks to modular perforation and cutting unit
- The print roller can be changed in 30 seconds
- High output, 250 Dekafix markers/min.

**General ordering data**

Type	Order No.	Version	GTIN (EAN)	Qty.
THM MMP	<a href="#">1302920000</a>		4050118102307	1 pc(s).
EXT.RH				