

**SwitchMark
SM 27/12.5 MM WS**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

**Prevention of incorrect operation: SM**

MultiMark device markers can be used with marking materials from different manufacturers. Wherever they are used, they ensure that all components, such as control and signalling devices from different vendors, are clearly assigned.

Your benefits with MultiMark

- Double laminated polyester
- Can be used with equipment from many manufacturers
- Device markers with a familiar design

General ordering data

| | |
|--------------------|---|
| Type | SM 27/12.5 MM WS |
| Order No. | 2006500000 |
| Version | SwitchMark, Device markers, 12.5 x 27 mm, white |
| GTIN (EAN) | 4050118391367 |
| Qty. | 1,000 pc(s). |
| compatible printer | 2430920000 2448870000 |

Data sheet

SwitchMark SM 27/12.5 MM WS

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

| | | | |
|------------|---------|-----------------|------------|
| Width | 27 mm | Width (inches) | 1.063 inch |
| Height | 12.5 mm | Height (inches) | 0.492 inch |
| Depth | 0.1 mm | Depth (inches) | 0.004 inch |
| Net weight | 0.12 g | | |

General data

| | | | |
|-----------------------------|-----------------------------|---------------------------|-------|
| Adhesive | Acrylate adhesive | Approval acc. to UL 969 | Yes |
| Colour | white | Halogen | No |
| Material | Polyester | Number per roll | 1,000 |
| Operating temperature range | -40...120 °C | UL 94 flammability rating | V-0 |
| Version | halogen-free, Self-adhesive | Width | 27 mm |

Classifications

| | | | |
|------------|-------------|------------|-------------|
| ETIM 6.0 | EC001288 | eClass 6.2 | 27-37-12-25 |
| eClass 9.0 | 27-40-06-29 | eClass 9.1 | 27-40-06-29 |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|------------------|------------------------------|
| Engineering Data | EPLAN, WSCAD |
| Engineering Data | STEP |

Data sheet

**SwitchMark
SM 27/12.5 MM WS**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings



**SwitchMark
SM 27/12.5 MM WS**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Accessories

Ink ribbons THM MMP



These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

General ordering data

| Type | Order No. | Version | GTIN (EAN) | Qty. |
|------------------------|----------------------------|------------|---------------|----------|
| RIBBON MM 76/360 SW | 2005080000 | Ink ribbon | 4050118389951 | 1 pc(s). |

Accessories / replacement parts



Our marking systems can be used to quickly and reliably label connector markers, conductor and cable markers, device markers and labels. The M-Print® PRO software enables rapid and easy identification of your electrical equipment. You can design, label and order your marking materials professionally and quickly. Frames, barcodes, graphics or photos are easily incorporated. The versatile data conversion routines enable quick and flexible data integration. The Weidmüller PrintJet ADVANCED, MCP Plus and MCP Basic printers and the THM series printers are available for printing.

General ordering data

| Type | Order No. | Version | GTIN (EAN) | Qty. |
|-----------------------|----------------------------|---------|---------------|----------|
| THM MMP ROLLER 115 | 1357420000 | | 4050118160314 | 1 pc(s). |