



Main

Accessory / separate part type	Cable
--------------------------------	-------

Complementary

Accessory / separate part designation	Bare cable
Accessory / separate part category	Cabling accessories
Cable length	25 m
Material	PvR (PVC/NBR) sheath
Colour	Matt black
Cable cross section	0.5 mm ²
Total number of wires	4
Wire insulation material	PVC
Flame retardance	Class C2 conforming to NF C 32-070
[Ue] rated operational voltage	300 V
[Ui] rated insulation voltage	2000 V conforming to NF C 32-201-1
Bending radius	Minimum 3 x external diameter
Tensile strength	10...35 N/mm ²
Hardness	70 shores A (tolerance: +/-5)
Product weight	1.115 kg

Environment

Ambient air temperature for operation	-35...90 °C
Ambient air temperature for storage	-40...100 °C
Environmental characteristic	Synthetic oils at 90 °C Soluble resistant at 90 °C Mineral resistant at 90 °C Without unmoulding agent Without silicone

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 0601 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
------------------------	---

Contractual warranty

Warranty period	18 months
-----------------	-----------
