



- Preheat plate
- 600 W, 230 V
- Board size upto 120 x 190 mm
- Temperature range 50 °C - 400 °C
- Digital display for set and actual temperature
- Digitally controlled
- 2 heated zones can be selected
- External sensor (accessory) connectable
- RS 232-Interface cable e.g. for connection to WHA 3000 hot air station
- Easy Fix board holder
- K-type thermo couple socket for monitoring

WHP 3000 Infrared preheating plate

Product no.: T0053338699N

Dimensions L x W x H (mm)	254 x 395 x 70 mm
Dimensions L x W x H (inches)	10 x 15.55 x 2.76 Inch
Weight (approx.) in kg	---
Voltage	230 V, 50/60 Hz
Power	600 W
Channels	---
Temperature range (depends on tool) °C	---
Temperature range (depends on tool) °F	---
Temperature accuracy °C	---
Temperature accuracy °F	---
Temperature accuracy for hot air °C	---
Temperature accuracy for hot air °F	---
Temperature stability °C	---
Temperature stability °F	---
Equipotential bonding socket	---
Display	---
Additional vacuum pump	---
Max. hot air flow rate l/min (depends on tool)	---
Capacity l/min	---
Max. vacuum	---
Interface	1 x RS232, 1 x thermocouple type K