

WXR 3030

3-Channel Rework Station, 420 W (600 W)
Product no.: T0053501699N



Benefits


- Power unit WXR 3, 3 channels with WXHAP 200 Hot air iron, WXDP 120 Desoldering iron and WXP 65 Soldering iron




For this purpose, we recommend:



Solder fume extractors



Soldering irons



Cleaning




Pre-heating plates



Technical Data

Dimensions L x W x H (mm)	273 x 235 x 102
Dimensions L x W x H (inches)	10,75 x 9,25 x 4,02
Weight (approx.) in kg	6.7
Voltage	230 V (50/60 Hz)
Power	420 W (600 W)
Channels	3
Temperature range (depends on tool) °C	100 - 450 (550)
Temperature range (depends on tool) °F	200 - 850 (999)
Temperature accuracy °C	±9
Temperature accuracy °F	±17
Temperature stability °C	±2
Temperature stability °F	±4
Equipotential bonding socket	Via 3.5 mm pawl socket on back of device (Hard grounded)
Display	255 x 128 dots / Backlighting
Air consumption l/min	---
Operating pressure in bar/psi	---
Capacity l/min	18
Vacuum	---

Owning the bench



PROFESSIONAL



FILTRATION



EREM



XCELITE