

XCSL761B3

SAFETY LIMIT SW+SOLENOID+1/2 NPT ENTRY

Main

Actuator Type	Key
Ampere Rating	10A
Approvals	UL Listed File Number: E164353 CCN NKCR - CSA Certified File Number: LR4408794 Class 3211 03 - CE Marked
Connection Type	(1) 0.5 Inch NPT (Conduit Entrance)
Contact Configuration	1 N.O.(staggered)/2 N.C.
Contact Operation	Slow Break (Break before Make)
Depth	1.73 Inches
Enclosure Material	Metal
Enclosure Rating	NEMA 1/2/3/4/12 - IP67
Enclosure Type	Water tight, Dust tight and Ice resistant (Indoor/Outdoor)
Height	7.64 Inches
Lock Method	Inserting Actuating Key
Maximum Voltage Rating	300VAC
Number of Poles	3-Pole
Operating Temperature Range	-13 to 158 Degrees F
Orientation	Actuating Key: Front - Connection: Left
Pilot Light	Orange LED
Supply Voltage	24VDC
Terminal Type	Screw Clamp
Type	XCSL
Unlock Method	Powering Electromagnet
Weight	32 Ounce
Width	2.99 Inches
Wire Size	#14 to #20 AWG

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.