SCS WRIST STRAP SELECTION GUIDE

Environmental Type

Band	Field Service	Standard Industrial	Critical		
Metal	Х	X	Х		
Elastic	Х	X			
Disposable	Х	X (Visitors)			

Single-Wire

Dual-Wire

Wristband	<u>Adjustable</u> <u>Fabric</u>	<u>Metal</u>	<u>Thermoplastic</u>	<u>Disposable</u>	Adjustable Fabric	<u>Metal</u>	<u>MagSnap 360™</u> <u>Metal</u> <u>Expansion</u>	<u>MagSnap</u> <u>360™</u> Thermoplastic	<u>Thermoplastic</u>
Band Material	Elastic nylon	Stainless steel	Thermoplastic	Insulative spunbonded polyester non- woven fabric outer material	Elastic nylon	Expandable metal	Expandable metal	Thermoplastic	Thermoplastic
Coil Cord	4mm Stud / 5 ft., 6 ft., 10 ft., 12 ft. Coil Cord	4mm Stud / 6ft. or 12 ft. Coil Cord	4mm Stud / 5ft. Coil Cord	N/A	N/A	5 ft. Coil Cord	6 ft. or 12 ft. Coil Cord	6 ft. or 12 ft. Coil Cord	N/A
Band Size	Adjustable	Fixed	Adjustable	Adjustable	Adjustable	Fixed	Fixed	Adjustable	Adjustable
Color	Blue, Burgundy, Light Blue w/ White, Maroon	Black, Light Blue	Blue	White / Black	Light Blue	Black	Black	Blue	Blue
Part Numbers	2204, 2214, 2224, 2271, 2272, ECWS61M-1, WBB-AFWS, WBB-AFWS61M, WBB-AFWS121M	<u>2205, 2206, 2207,</u> <u>AMWS, AMWS61M,</u> <u>AMWS121M</u>	<u>4620.</u> <u>4650</u>	<u>2209</u>	<u>2368</u>	<u>2381, 2382,</u> <u>2383, 2384,</u> <u>2385, 2386</u>	<u>2228, 2229,</u> <u>2230, 2231,</u> <u>2232, 2233</u>	<u>2240, 2241,</u> <u>2242</u>	<u>4720</u>
Country of Origin	United States of America, Taiwan	China, Philippines	United States of America	United States of America	United States of America	United States of America	United States of America	United States of America	United States of America

SCS Wrist Straps meet the requirements of ANSI/ESD S20.20 and Wrist Strap standard ANSI/ESD S1.1



926 JR Industrial Drive, Sanford, NC 27332 East: 919-718-0000 | West: 909-627-9634 StaticControl.com

