

Product data sheet

Characteristics

XVMC37

illuminated unit - Ø 45 - clear - BA 15d - bulb not included - ≤ 230 VAC DC



Main

Range of product	Harmony XVM
Product or component type	Indicator bank
Beacon or indicator bank unit type	Illuminated unit
Component name	XVM
Light source	Clear bulb not included
Bulb type	Flash discharge tube Incandescent with BA 15d base Super bright LED
[Us] rated supply voltage	≤ 230 V AC/DC

Complementary

Mounting diameter	45 mm
Assembly style	Customer assembly
Power dissipation in W	≤ 5 W
Connections - terminals	Screw terminals: 1 x 0.325...1 x 1.5 mm ²
Marking	CE
[Ui] rated insulation voltage	250 V conforming to IEC 60947-1
Nominal voltage limit	0.85...1.1 Un conforming to IEC 60947-5-1
[Uimp] rated impulse withstand voltage	4 kV conforming to IEC 60947-1
Luminance	650 cd/m ²
CAD overall width	47 mm
CAD overall height	65 mm
CAD overall depth	47 mm
Product weight	0.04 kg

Environment

Product certifications	CCC
Standards	EN/IEC 60947-5-1 EN/IEC 60947-1
Ambient air temperature for storage	-25...70 °C
Ambient air temperature for operation	-10...50 °C
IP degree of protection	IP40 in any position except vertical position conforming to IEC 60529

IP42 in vertical position conforming to IEC 60529

Electrical shock protection class	Class I aluminium tube mounting conforming to IEC 60947-1 Class I aluminium tube mounting conforming to IEC 60947-5-1 Class I aluminium tube mounting conforming to IEC 61140 Class II base mounting conforming to IEC 60947-1 Class II base mounting conforming to IEC 60947-5-1 Class II base mounting conforming to IEC 61140
Protective treatment	TC


Contractual warranty

Warranty period	18 months
-----------------	-----------

Customer Assembled Tower Light

Dimensions

Below drawing shows a tower light with 3 illuminated stages. Select the number of stages according to the product characteristics in order to get b dimension.



- (1) Cover (included with base unit XVMC21/C29•)
- (2) Illuminated unit
- (3) Base unit XVMC21 (without buzzer) or XVMC29• (with buzzer), to be ordered separately
- (4) Fixing base XVMZ0•/Z0•T, to be ordered separately

Number of illuminated units (ref. 2)	b in mm	b in in.
1	127	5.00
2	192	7.56
3	257	10.12
4	322	12.68
5	387	15.24