

Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Protect It! 8-Outlet Surge Protector, 8 ft. Cord, 1440 Joules, Black Housing

MODEL NUMBER: TLP808B











Safeguard your workstation or home electronics against surges, spikes and line noise. Ideal for protecting your computer, printer, scanner, external hard drive and other sensitive electronics.

Description

Perfect for your home or office workstation, the TLP808B Protect It! 8-Outlet Home-Computer Surge Protector features a surge suppression rating of 1440 joules to defend your sensitive electronic components against strong surges and spikes. In fact, Tripp Lite will repair or replace any connected equipment damaged by surges, including direct lightning strikes, up to \$75,000 for life (valid in the U.S., Canada and Puerto Rico only).

The TLP808B includes full normal mode (H-N) and common mode (N-G/H-G) line surge suppression, as well as technology that filters out disruptive EMI/RFI line noise, preventing interference from disrupting your electronics and inflicting damage or data loss.

Your computer and peripherals plug into eight NEMA 5-15R outlets, including three widely spaced outlets designed to accept bulky transformers without blocking adjacent outlets. Built-in child-safety covers block accidental contact with unused outlets. Integrated 15-amp circuit breaker protects all outlets against dangerous overloads. Lighted on/off switch provides one-touch control over connected equipment. LEDs indicate protection status and that your wall outlet is properly grounded.

The eight-foot AC power cord allows the TLP808B to reach distant outlets, while its right-angle NEMA 5-15P plug allows furniture and equipment to be moved flush against the wall to save space in your workstation. Keyhole slots on the bottom panel provide convenient wall or desk mounting options.

Features

1440-Joule Surge Protection for Home or Office Electronics1440-joule rating protects your computer, printer, scanner, external hard drive and other sensitive electronic components against even the strongest surges and spikesBacked by Tripp Lite's \$75,000 Ultimate Lifetime Insurance for any connected components damaged by power surge (U.S., Canada and Puerto Rico only)Full normal mode (H-N) and

Highlights

- 8 NEMA 5-15R outlets, including 3 for bulky transformers
- Surge suppression rating of 1440 joules
- Filters out threatening EMI/RFI line noise
- 15A resettable circuit breaker prevents dangerous overloads
- 8 ft. AC power cord with rightangle NEMA 5-15P plug

Package Includes

- TLP808B Protect It! 8-Outlet
 Surge Protector, Black Housing
- Owner's manual



common mode (N-G/H-G) line surge suppressionFilters out disruptive EMI/RFI line noise that can cause equipment damage or data lossExceeds IEEE 587 Category A and B surge suppression specifications 8 Outlets Accept Wide Range of Electronic Devices 8 NEMA 5-15R AC outlets accept most computers and peripherals 3 widely spaced outlets accommodate bulky transformers without blocking other outletsBuilt-in child-safety covers block accidental contact with unused outlets

Premium Safety FeaturesLighted on/off switch provides one-touch control over connected equipmentAutomatic shutoff permanently cuts power to outlets if protection circuit is incapacitated, preventing equipment damage and indicating replacement is requiredLEDs show grounding and protection status at a glance

Fits Effortlessly Into Your Workstation8 ft. AC power cord long enough to reach distant outletsSpace-saving right-angle NEMA 5-15P plug allows furniture and equipment to move flush against the wallKeyhole slots on bottom panel provide convenient wall or desk mounting optionsBlack plastic housing designed for long life

Auto-ShutdownAutomatic shutoff permanently cuts power to outlets if protection circuit is incapacitated, preventing equipment damage and indicating replacement is required

Specifications

OVERVIEW		
UPC Code	037332189837	
ОИТРИТ		
Frequency Compatibility	50 / 60 Hz	
Output (Watts)	1800	
Output Receptacles	(8) 5-15R	
Circuit Breaker (amps)	15	
Transformer Accommodation	(6) Yes	
Outlet Orientation	Single row of 5, plus a second row of 3 for transformer accommodation	
Right-Angle Outlets	No	
INPUT		
Nominal Input Voltage(s) Supported	120V AC	
Recommended Electrical Service	120V (110-125V)	
Input Cord Gauge Type	14 gauge; SJT	
Voltage Compatibility (VAC)	120	
Maximum Surge Amps	84000	
Input Plug Type	NEMA 5-15P	
Input Cord Length (ft.)	8	
Right-Angle Plug	Yes	
Input Cord Length (m)	2.44	
Integrated Cord Clip	No	
USER INTERFACE, ALERTS & CONTROLS		





Diagnostic LED(s)	Yes
Switches	Combination AC circuit breaker and 2 position red illuminated on/off power switch
Diagnostic LED Details	Built-in LEDs confirm suppressor "protection present" (green) and "grounded" (red) status
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	1440
AC Suppression Response Time	< 1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression
Clamping Voltage (RMS)	150
UL1449 Let Through Rating	330 L-G, 400 L-N, 400 N-G
EMI / RFI Filtering	Up to 40 dB
Auto Shut-Off	Yes
DATALINE SURGE SUPPRESSION	
Telephone/DSL Protection	No
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
PHYSICAL	
Shipping Dimensions (hwd / in.)	2.00 x 7.50 x 11.50
Shipping Dimensions (hwd / cm)	5.08 x 19.05 x 29.21
Shipping Weight (lbs.)	2.00
Shipping Weight (kg)	0.91
Unit Dimensions (hwd / in.)	4.86 x 9.55 x 1.51
Unit Dimensions (hwd / cm)	12.34 x 24.26 x 3.84
Unit Weight (lbs.)	1.76
Unit Weight (kg)	0.80
Material of Construction	Plastic
Integrated Keyhole Mounting Slots	Yes
Housing Color	Black
Receptacle Color	Gray
Color (AC Line Cord)	Black
Color	Black
Outlets Measurement (Center to Center)	Distance between standard outlets = 28.5mm; Distance between transformer outlets = 57mm
Anti-Microbial Protected	No



Tripp Lite1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234

CERTIFICATIONS		
UL1449 3rd Edition (AC Suppression)	UL1449 3rd Edition	
UL1363 (Power Tap)	UL1363	
Canada	cUL	
Approvals	Exceeds IEEE 587 category A&B specifications	
WARRANTY		
Product Warranty Period (Worldwide)	Lifetime limited warranty	
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$75,000 Ultimate Lifetime Insurance	

© 2019 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: https://www.tripplite.com/products/product-certification-agencies