


3/8-32 UNEF-2B
THREAD



Ø0.386
REF

NOTES:

1. MATERIALS:
COVER & BASE - STEEL
FINISH - POLYESTER POWDER COAT,
SEMI-GLOSS NAVY GRAY - 26187

GASKET - SYNTHETIC RUBBER
TORSION SPRING - STAINLESS STEEL
AXLE - COPPER ALLOY, NICKEL PLATED
NUT - COPPER ALLOY, NICKEL PLATED

- 2. HEX NUT SHIPPED UNASSEMBLED.
- 3. THIS PRODUCT IS RoHS COMPLIANT.

CUSTOMER DRAWING

THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.

					UNLESS OTHERWISE SPECIFIED 1. ALL DIMENSIONS IN INCHES - TWO PLACE DECIMALS ±0.02 - THREE PLACE DECIMALS ±0.005	SIZE	WIDTH	MULT	LBS/M	TEMPER	
						FINISH	MATERIAL				
						SPEC No.	SPEC No.				
						FIRST USED ON	SCALE 1.75:1				
						DATE DRAWN	BY	CHKD	APVD		
					9-19-06	RF	RF	TJK			
							9-19-06	9-19-07	SHEET 1 OF 1		
REV	ECO NUMBER	DATE	BY	APVD	DO NOT SCALE DRAWING	NAME				PART No.	REV
REVISIONS						JAX COVER, RoHS				520X	C

SolidWorks CAD File

