PLUGS



PCB TERMINAL BLOCKS

081 TERMINAL STRIPS

095

100 CIRCULAR CONNECTORS

151 IP68 CONNECTORS

158

Push-pull connectors female fixed socket CCM series



DEU type fixed socket, female contact

Code 1

0.9mm

Solder type

AWG 21-22

1300V(AC)

8.2A

≤250V

5000 mating cycles

Brass (gold plated)

<=95% [at 60°C /140°F]

15g [10 Hz - 2000 Hz]

100a [6 ms]

>72 hr

50/175/21

75 dB (10 MHz)

40 dB (1 GHz)

IP68 (when connected and using environmental cable clamp)

Brass (natural chrome plated) shell and collet nut, nickel plated brass latch sleeve and mid pieces

0.79mm

CCM1S1/03 3 pole

- · Premium range of circular connectors
- IP68 sealed using vacuum technology (when connected and using environmental cable clamp)
- Tough, high performance interconnection
- Compact panel mounting design
- · Ideal for harsh and extreme environments
- Suitable for broadcasting, autosport, military, rail, marine, security, industrial and agricultural applications
- Key coded to prevent misconnection
- · Will not disconnect when the cable is under load or stress
- · Tool slots for secure and tight mounting
- Tested to IEC 60512-3-5a



PART NO.	DESCRIPTION	POLES	SERIES
CCM1S1/03	Female fixed socket	3	CCM series



Shell style/model

Contact type

Max diameter

Rated current


Contact diameter

Max. stranded conductor

Vtest (contact-shell)

Vtest (contact-contact)

Codes



KEY FEATURES

Key coded | Deep panel mounting socket | Face slots for tightening with a tool

ACCESSORIES

Metal and rubber caps for sockets

PART NO.	DESCRIPTION	
CCT11	Camcirc metal cap for sockets A1	

|--|--|

PART NO.	DESCRIPTION	
CCT12	Camcric rubber cap for sockets A1	



ASSOCIATED PRODUCTS

CCA1P1/A03

- CCA Series A1 size plug

page 102



