

The Only 1GHz Passive Probes In The Market!

PERFORMANCE PASSIVE PROBES BRIDGE PERFORMANCE GAP WITH ACTIVE PROBES

Accurate High-speed Passive Probes

- 1 GHz bandwidth
- 10 MΩ, <4 pF input impedance
- 10X attenuation factor
- 300 V CAT II input voltage
- -15°C to +65°C operating temperature
- Wide variety of connectivity accessories

Sales Promotion

- **Buy 1 TPP1000 probe, get another one free**
- Available from July 8th, 2019 to December 31st, 2019
- Please reference MSR **525-1005** when asking CSRs to generate applicable quotes

promotion

TPP1000 Probe & Standard Accessories



Optional Accessories

Description	Image
MMCX probe tip, gold (TPP1000 only) ¹	
MMCX to 0.1 in. (2.54 mm) sq. pin adapter, blue, 0.025 in. (0.635 mm) sq. pins (TPP1000 only)	
MMCX to 0.062 in. (1.57 mm) sq. pin adapter (white), 0.016 - 0.018 in. (0.4 - 0.46 mm) sq. pins (TPP1000 only)	
Electrical Y-Lead (TPP1000 only)	
Alligator ground (12 in.)	
6 in. clip-on ground lead (with 0.025 in. pin receptacle)	
Microcircuit test tip	
Compact probe tip chassis mount test jack (TPP0502 and TPP1000 only)	
BNC to probe tip adapter	
PCB to probe tip adapter, pack of 10	
Compact probe tip chassis mount test jack (TPP0250 and TPP0500B only)	
Color bands (set of 4 color-coded bands)	
Tweaker tool	
DUT Interface pin kit with (qty. 20) 0.018 in. (0.46 mm) round solder-in pins (TPP1000 only)	
Solder aid for 0.062 in. (1.57 mm) pitch sq. pins, 0.016 - 0.018 in. (0.4 - 0.46 mm) sq. pins (TPP1000 only)	
Probe tip tripod support with living hinge ²	



Best Passive Probe In The Market!