

6 ft. (1.8 m) Cisco USB Console Cable - USB to RJ45

Product ID: ICUSBROLLOVR



This Cisco USB console cable offers a reliable connection from your desktop or laptop to networking equipment that features a console port.

Compatible USB Connection

Create a direct connection from the USB 2.0 port on your computer or laptop to the RJ45 console port on your router, server, firewall or switch. This Cisco rollover cable is compatible with most routers, including Cisco, Juniper, Ubiquiti or TP-Link, providing an easy connection for programming your networking equipment from your Windows, Mac or Linux computer.

High-Quality Design

Expertly designed and constructed with only the highest quality materials, this USB to Ethernet cable provides maximum dependability, supporting data transfer rates up to 460Kbps. It also provides a reliable and hassle-free connection without the need for additional adapters or external power.

ICUSBROLLOVR is backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Connect a computer terminal to a router console port
- Configure your networking equipment through the USB port on your laptop or desktop computer
- Connect laptops to compatible routers, servers or firewalls

Features

- Directly connect a USB-equipped laptop or desktop to a router console, without the need for an adapter
- Supports connections to network devices that feature a console port
- Maximum compatibility with Cisco®, Juniper®, Ubiquiti® or TP-Link® routers
- Supports a direct USB console connection, with no additional adapters
- Constructed of high-quality materials, supports transfer rates of up to 460Kbps

Hardware	Warranty	2 Years
	Bus Type	USB 2.0
	Cable Jacket Type	PVC - Polyvinyl Chloride
	Chipset ID	Prolific PL2303HXD
	Industry Standards	USB 1.1/2.0, RS-232
	Port Style	Cable Adapters
	Ports	1
Performance	Data Bits	5, 6, 7, 8
	FIFO	512 Bytes
	Max Baud Rate	460.8 Kbps
	Parity	Odd, Even, Mark, Space, or None
	Stop Bits	1, 1.5, 2
	Supported Protocols	RS-232
Connector(s)	Connector A	1 - USB Type-A (4 pin) USB 2.0 Male
	Connector B	1 - RJ-45 Male
Software	OS Compatibility	Windows® 7, 8, 8.1, 10 Windows Server® 2008 R2, 2012, 2012 R2, 2016 Mac OS® 10.6 to 10.14 Linux 2.4.31 to 4.11.x <i>LTS version only</i>
Special Notes / Requirements	System and Cable Requirements	One available USB 1.1 (or above) port
Power	Power Source	Bus Powered
Environmental	Humidity	20~80% RH
	Operating Temperature	0°C to 70°C (32°F to 158°F)
	Storage Temperature	-20°C to 80°C (-4°F to 176°F)
Physical Characteristics	Cable Length	6 ft [1.8 m]
	Color	Black
	Enclosure Type	Plastic
	Product Height	0.4 in [1.1 cm]
	Product Length	6 ft [1.8 m]
	Product Width	0.9 in [23.4 mm]
	Weight of Product	1.4 oz [40 g]

	Wire Gauge	28 AWG
Packaging Information	Package Height	1.2 in [30 mm]
	Package Length	6.7 in [17 cm]
	Package Width	5.6 in [14.2 cm]
	Shipping (Package) Weight	3.5 oz [98 g]
What's in the Box	Included in Package	1 - USB to RJ45 Rollover Cable 1 - Quick-Start Guide
	Connector Plating	Nickel

Product appearance and specifications are subject to change without notice.