


ASSEMBLY NO.	LED COLOR	I _V (MIN)	V _F (MAX)	λ _{PEAK}	TEST COND.	I _R (MAX)@5V
550-6207F	GREEN	8.7 mcd	2.8V	565nm	I _F = 20mA	100μA
550-6307F	YELLOW	5.6 mcd	2.8V	585nm	I _F = 20mA	100μA

REV.	ECN NO.	REVISIONS	DRN.	CKD.	APP.	DATE
A	—	NEW RELEASE	JMC	—	N.O.	3-29-94
B	—	P/N 550-6_-07 WAS 552-6_-07	JMC	—	N.O.	1-27-95
C	—	REVISED LED SPECS; ADD NOTE 3	TC	DC	NO	1-20-99
D	—	REMOVED P/N 550-6407F. ADDED F SUFFIX FOR P/N 550-6207F/6307F	BP	—	NO	9-22-16



NOTES:

- LAMP MUST BE SEATED ALL THE WAY DOWN INTO HOUSING, BENDS MUST BE TIGHT, NO LONGITUDINAL TRAVEL ALONG AXIS ALLOWED.
- "*" DENOTES CRITICAL DIMENSION.
- DIALIGHT PART NUMBER: 550-6X07F.

THIS DRAWING AND THE CONTENTS HEREIN ARE CONFIDENTIAL AND THE SOLE PROPERTY OF DIALIGHT. REPRODUCTION OF THIS DRAWING OR CONSTRUCTION OF ANY PARTS WITHIN THIS DRAWING ARE FORBIDDEN WITHOUT THE WRITTEN CONSENT OF DIALIGHT.		
SCALE: DRAWING SCALE ALL DIM'S IN: INCHES (MM)	DRAWING NUMBER C-15866	REV D
TOLERANCES: UNLESS OTHERWISE SPECIFIED FRACTIONS: ±1/64 DECIMALS (.XX): ±.020 DECIMALS (.XXX): ±.005 DECIMALS (.XXXX): ±.0005 ANGLES: ±3°	TITLE	
FINISH:	MATERIAL	
FSCM 83330	Dialight 1501 ROUTE 34 SOUTH FARMINGDALE, NJ 07727	
SHEET 1 OF 1	FAMILY TABLE:	