

# WT 1010

1-Channel Soldering Station set, 95 W with soldering iron WTP 90  
Product no.: T0053436699N



## Benefits

- › Power unit WT 1, 1 channel with soldering iron WTP 90 and safety rest WSR 200
- › WTP 90: The soldering iron (90 W) for universal use with power response tips. Tip family XNT & XH (high mass tips)
- › OFF time, Process window, Lock function, Offset



### Technical Data

Dimensions L x W x H (mm)	149 x 138 x 101
Dimensions L x W x H (inches)	5.87 x 5.43 x 3.98
Weight (approx.) in kg	1.9
Voltage	230 V, 50/60 Hz
Power	95 W
Channels	1
Temperature range (depends on tool) °C	100 - 450
Temperature range (depends on tool) °F	150 - 850
Temperature accuracy °C	±9
Temperature accuracy °F	±17
Temperature stability °C	±2
Temperature stability °F	±4
Equipotential bonding socket	Via 3,5 mm pawl socket on front of device
Display	Backlit LCD
Air consumption l/min	---
Operating pressure in bar/psi	---
Capacity l/min	---
Vacuum	---

## 522N

Side cutter – oval head

Article number: 522N



### Technical Data:

Length mm	115
Weight	67 g
Length of cutting edges mm	12
Head width mm	11
Head thickness mm	6
Head length mm	19
Max. Cutting capability - hard wire mm	-
Max. Cutting capability - medium hardness mm	Ø 1.0
Max. Cutting capability - copper wire mm	Ø 1.6
Length inches	4.528
Series	500
Length of cutting edges Inches	0.472
Head width inches	0.433
Head thickness inches	0.236
Head length inches	0.748
ESD-safe	on