

Han Guiding PE module, female



| Part number | 09 14 003 3152 |
|--------------------|-------------------------------------|
| Specification | Han Guiding PE module, female |
| HARTING eCatalogue | https://b2b.harting.com/09140033152 |

Identification

| Category | Modules |
|---------------------------|---------------------------------|
| Series | Han-Modular [®] |
| Type of module | Han [®] Guiding module |
| Description of the module | PE module |

Version

| Termination method | Crimp termination |
|--------------------|---|
| Gender | Female |
| Number of contacts | 2 |
| PE contact | Yes |
| Details | Please order crimp contacts separately. |
| | Not for Han-Modular [®] hinged frames! |

Technical characteristics

| Conductor cross-section | 0.14 4 mm² |
|-------------------------|---------------------|
| Rated current | 16 A |
| Rated voltage | 500 V |
| Rated impulse voltage | 6 kV |
| Pollution degree | 3 |
| Insulation resistance | >10 ¹⁰ Ω |
| Limiting temperature | -40 +125 °C |
| Mating cycles | ≥500 |
| Lock-in range | ±4 mm |



Material properties

| Material (insert) | Polycarbonate |
|---|------------------------|
| Colour (insert) | RAL 7032 (pebble grey) |
| Material flammability class acc. to UL 94 | V-0 |

Specifications and approvals

| Specifications | EN 60664-1 |
|----------------|------------|
| | IEC 61984 |

Commercial data

| Packaging size | 2 |
|--------------------------------|------------|
| Net weight | 9.2 g |
| Country of origin | China |
| European customs tariff number | 8547200000 |