




Surface mounting enclosure, flat, 1 mounting location, M30

Part no. **M30-FI1**
 Catalog No. **197235**

Delivery program

Basic function accessories			Surface mounting enclosure
Housing			Insulated material
			With high-grade steel screws
Number of locations		Qty.	1
Cable entry knockouts			
Cable entry			rear: 1 x M20 lateral: 1 x M20
Degree of Protection			IP66, IP67, IP69
Impact resistance			IK06 according to EN 50102
Colour			
			
RAL Value			RAL 7035
Colour			Enclosure base anthracite
Connection to SmartWire-DT			no
For use with			1 x Ø 30.5
For use with			(Illuminated) pushbuttons (Illuminated) selector switches Key-operated pushbuttons Indicator light EMERGENCY STOP/EMERGENCY OFF buttons with yellow set of adapter rings M22Y-R30 Flat rear contact elements M22-FK... Flat Rear LED elements M22-FLED-...
Actuator travel and actuation force as per DIN EN 60947-5-1, K.5.4.1			
Minimum force for positive opening	N		0

Technical data

General

Degree of Protection			IP66, IP67, IP69
Ambient temperature			
Open		°C	-25 - +70

Design verification as per IEC/EN 61439

Technical data for design verification			
Operating ambient temperature min.		°C	-25
Operating ambient temperature max.		°C	70
Impact resistance			IK06 according to EN 50102

Technical data ETIM 7.0

Number of command positions		1
Construction type housing		Surface mounting housing
Material housing		Plastic
Material quality housing		Other
Diameter openings	mm	30
Colour housing cover		Grey
Degree of protection (IP)		IP67/IP69K
Degree of protection (NEMA)		
Width	mm	43
Height	mm	131,5
Depth	mm	44

Dimensions

