

### THB.391.R4A

TeeTube micro sized, 4 Pole Multiple contact 7mm to 12mm, 4 mm max conductor size IP68 17.5A 450V in-line Xdry anti condensation connector



#### SPECIFICATION

Cable Entries	2
Number of Poles	4
Terminal Type	Screw - end barrier contact
Body Material	PA66 / TPE
Colour	Black/green (seals)
IP Rating	68
Max Conductor Size (Sq mm)	4
Max Current (A)	17.5
Max Voltage (V)	450
Minimum Temp Rating °C	-40
Maximum Temp Rating °C	125
Minimum Cable Diameter (mm)	7
Maximum Cable Diameter (mm)	12
Fixing System	Cable
Temperature "T" Rating	T85