

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0190170047

Status:


Active

Overview:

Standard Quick-Disconnect Terminals

Description:

InsulKrimp Quick Disconnect, Female, for 10-12 (5.00-3.30mm²) Wire, Box, Tab 6.35 x 0.81mm



Documents:	
3D Model	Product Specification 194130100-000 (PDF)
Drawing (PDF)	Product Specification PS-19902-011-001 (PDF)
Product Specification 194130096-000 (PDF)	Product Specification PS-19902-013-001 (PDF)
Product Specification 194130099-000 (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification	
CSA	LR18689
UL	E79133
General	
Product Family	Quick Disconnects
Series	19017
Crimp Quality Equipment	Yes
Insulated	Partial
Overview	Standard Quick-Disconnect Terminals
Product Name	InsulKrimp
Type	Quick Disconnect
UPC	800753036345
Physical	
Barrel Type	Closed
Color - Resin	Yellow
Flammability	94V-0
Gender	Female
Glow-Wire Capable	No
Insulation	PVC
Lock to Mating Part	None
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	PVC
Net Weight	1.297/g
Orientation	Straight
Packaging Type	Bag
Polarized to Mating Part	No
Tab Thickness	0.81mm
Tab Width	6.35mm
Temperature Range - Operating	-50° to +105°C
Wire Insulation Diameter	6.40mm max.
Wire Size AWG	10, 12
Electrical	
Voltage - Maximum	600V
Solder Process Data	
Lead-freeProcess Capability	N/A
Material Info	
Engineering Number	C-2143
Reference - Drawing Numbers	

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per	
-ED/88/2018 (15	
January 2019)	
Halogen-Free	
Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

19017 Series

Product Specification

Sales Drawing

194130096-000, 194130099-000, 194130100-000,
PS-19902-011-001, PS-19902-013-001
SD-19017-003

This document was generated on 07/25/2019

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION