



# Energizer Industrial® Vision HD Headlight

The Energizer® Industrial Vision HD headlight is another innovative headlight solution from the Energizer® premium headlight line. With the latest LED technology, users get an extremely bright, lightweight hands-free solution with ample run time capability. Patented optics offer exceptional direct and peripheral vision, making the Energizer® Vision HD a perfect light for home, work and outdoor activities. Thanks to the advanced dimming feature, users can control the intensity of light from 100% to 10%, and enjoy Next Push Off technology to avoid unnecessary switch cycles. With an adjustable head strap, water-resistant design and pivoting head to direct light exactly as needed, this headlight is another way Energizer® continues to deliver innovative lighting solutions.

## Design Benefits

- ✓ **Advanced dimming feature** to control light intensity in Spot + Flood Mode
- ✓ Silicone beading on head strap for extra grip
- ✓ Next Push Off to avoid unnecessary switch cycles
- ✓ IPX4 water resistant and shatterproof lens construction
- ✓ Pivoting head to direct light where needed

## Performance Benefits

- ✓ Up to 4X brighter than standard LED technology
- ✓ Patented optics, delivering exceptional direct and peripheral vision
- ✓ Long runtime

## Light and Power Source

- ✓ Features LED technology
- ✓ Operates on 3AAA batteries
  - ✓ (Includes 3AAA Energizer MAX® batteries)



--	--	--	--	--

### 4 Operating Modes + Dimming Feature

Mode	Lumens	Runtime	Beam Distance	Impact Resistant	Water Resistant
High (Spot and Flood Combined)	200	8.5hrs	50m	1m	IPX4
Low (Spot and Flood Combined Dimmed)	30	50hrs	-	1m	IPX4
Spot	145	13hrs	-	1m	IPX4
Flood	70	30hrs	-	1m	IPX4