

Printed-circuit board connector - PC 6/ 2-ST-BUS-7,62 - 1044740

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



PCB connector, nominal current: 32 A, number of positions: 2, pitch: 7.62 mm, connection method: Displacement connection, color: green, contact surface: Tin

The figure shows a version of the product

Your advantages

- ✓ Easy looping through of high power ratings using standard 16 mm² conductors (H07V-K)
- ✓ Connection without conductor pretreatment for huge time savings
- ✓ Drive screw position easily recognizable, thanks to indicator
- ✓ Application-specific insulation thanks to individually removable insulating caps



Key Commercial Data

Packing unit	1 pc
Minimum order quantity	20 pc
GTIN	 4 055626 622842
GTIN	4055626622842
Custom tariff number	85366990
Country of origin	Slovakia

Technical data

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Printed-circuit board connector - PC 6/ 2-ST-BUS-7,62 - 1044740

Classifications

eCl@ss

eCl@ss 8.0	27440309
eCl@ss 9.0	27440309

ETIM

ETIM 5.0	EC002638
ETIM 6.0	EC002638

Approvals

Approvals

Approvals

cULus Recognized

Ex Approvals

Approval details

cULus Recognized		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	E60425-20010727
	B	C	
Nominal voltage UN	600 V	600 V	
Nominal current IN	30 A	30 A	
mm ² /AWG/kcmil	6	6	

Accessories

Accessories

Coding element

Coding profile - CP-PC RD - 1701967

Coding profile, for plugging into the coding ribs of the plug at a later date, insulating material, color: Red



Printed-circuit board connector - PC 6/ 2-ST-BUS-7,62 - 1044740

Accessories

Insulator cap

Insulating part - EC-PC 6/ 2-ST-BUS - 1044822



Insulating part, number of positions: 2, pitch: 0 mm, color: green

Screwdriver tools

Screw insert - SF-BIT-TX 15-50 - 1212576



Screw bit, Torx[®], E6.3-1/4" drive, size: TX 15 x 50 mm, hardened, suitable for holder according to DIN 3126-F6.3/ISO 1173

Tool set

Tool set - SF-LTX SET - 1200162



Offset screwdriver set, Torx, metric, TX 8, 9, 10, 15, 20, 25; 27, 30, 40 mm, 9-piece, BlackLaser surface, in practical holder

Tool set - SF-M SET - 1212543



Bit screwdriver set with quick-action chuck, 89 mm long slotted/crosshead (PZ and PH)/hex/Torx[®] bits, 17-part, in folding belt pouch, contents: PH 1,2,3 x 89; PZ 1,2,3 x 89; SL 1.5 x 5.5 x 89; TX 10-30 x 89; SW 3,4,5,6 x 89

Additional products

Printed-circuit board connector - PC 6/ 2-ST-BUS-7,62 - 1044740

Accessories

Printed-circuit board connector - PC 6/ 2-G-7,62 - 1054546



PCB headers, nominal current: 41 A, number of positions: 2, pitch: 7.62 mm, color: green, contact surface: Tin, mounting: Wave soldering